

VISUALDSP++TM 2.0

C Compiler and Library

Manual for ADSP-218x DSPs

Revision 3.1, October 2001

Part Number
82-000400-03

Analog Devices, Inc.
Digital Signal Processor Division
One Technology Way
Norwood, Mass. 02062-9106



Copyright Information

©1996–2001 Analog Devices, Inc., ALL RIGHTS RESERVED. This document may not be reproduced in any form without prior, express written consent from Analog Devices, Inc.

Printed in the USA.

Disclaimer

Analog Devices, Inc. reserves the right to change this product without prior notice. Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use; nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under the patent rights of Analog Devices, Inc.

Trademark and Service Mark Notice

The Analog Devices logo, VisualDSP, the VisualDSP logo, SHARC, and the SHARC logo are registered trademarks; VisualDSP++, the VisualDSP++ logo, CROSSCORE, the CROSSCORE logo, TigerSHARC, the TigerSHARC logo, Blackfin, the Blackfin logo, EZ-KIT Lite, Apex-ICE, Mountain-ICE, Summit-ICE, Trek-ICE, and The DSP Collaborative are trademarks of Analog Devices, Inc.

Microsoft and Windows are registered trademarks and Windows NT is a trademark of Microsoft Corporation.

Adobe and Acrobat are registered trademarks of Adobe Corporation.

All other brand and product names are trademarks or service marks of their respective owners.

Rev. 3.1

CONTENTS

INTRODUCTION

Supported Processors	1-2
For Additional Product Information	1-2
For Technical or Customer Support	1-2
Purpose of This Manual	1-3
Intended Audience	1-3
Manual Contents Description	1-4
What's New in This Manual	1-4
Related Documents	1-5
Conventions	1-6

COMPILER

Overview	2-1
Compiler Command-Line Reference	2-3
Compiler Switch Descriptions	2-7
Data Type Sizes	2-34
C Compiler Language Extensions	2-36
Inline Function Support Keyword (inline)	2-39
Inline Assembly Language Support Keyword (asm)	2-40

CONTENTS

Assembly Construct Template	2-41
Assembly Construct Operand Description	2-44
Assembly Constructs With Multiple Instructions	2-47
Assembly Construct Reordering & Optimization	2-47
Assembly Constructs With Input & Output Operands	2-48
Assembly Constructs & Macros	2-49
Dual Memory Support Keywords (pm dm)	2-50
Memory Keywords & Assignments / Type Conversions	2-52
Memory Keywords & Function Declarations / Pointers	2-53
Memory Keywords & Function Arguments	2-54
Memory Keywords & Macros	2-54
Placement Support Keyword (section)	2-55
Boolean Type Support Keywords (bool, true, false)	2-56
Pointer Class Support Keyword (restrict)	2-56
Variable-Length Array Support	2-57
Non-Constant Aggregate Initializer Support	2-58
Indexed Initializer Support	2-59
Aggregate Constructor Expression Support	2-60
Preprocessor-Generated Warnings	2-61
C++-Style Comments	2-62
Compiler Intrinsic Functions	2-62
I/O Space for Read/Write	2-63
Read/Write of Non-Memory-Mapped Registers	2-63
Interrupt Control	2-64

Preprocessor Features	2-65
Predefined Macros	2-65
Header Files	2-68
Writing Macros	2-68
C Run-Time Model	2-70
Using the Run-Time Header	2-70
Interrupt Table and Interface	2-71
Stack Frame	2-72
Parts of the Stack Frame	2-74
General System-Wide Specifications	2-75
Return Values	2-76
Procedure Call and Return	2-77
Miscellaneous Information	2-78
Register Classification	2-78
Callee Preserved Registers (“Preserved”)	2-78
Dedicated Registers	2-78
Caller Save Registers (“Scratch”)	2-79
Circular Buffer Length Registers	2-79
Complete List of Registers	2-79
C and Assembly Language Interface	2-83
Writing C-Callable Assembly Routines	2-83
Calling C Routines From Assembler	2-86
Using Mixed C/Assembly Support Macros	2-87
Interface Support Macro Descriptions	2-87

CONTENTS

Using Mixed C/Assembly Naming Conventions	2-90
Compatibility Call	2-91
C Compiler Glossary	2-93

LIBRARY

Overview	3-1
C Run-Time Library Guide	3-2
Calling Library Functions	3-2
Using the Compiler's Built-In Functions	3-3
Linking Library Functions	3-3
Working With Library Source Code	3-4
Working with Library Header Files	3-4
asm_sprt.h – Mixed C/Assembly Support.....	3-6
assert.h.....	3-6
cctype.h.....	3-6
def2181.h – Memory Map Definitions.....	3-6
errno.h.....	3-7
ffts.h – Fast Fourier Transforms.....	3-7
filters.h – DSP Filters	3-7
float.h – Floating Point.....	3-8
fract.h – ADSP-218x Macro Fract Definitions.....	3-8
macros.h – Circular Buffers	3-8
math.h – Mathematics	3-8
misc.h – ADSP-218x DSP Timer Functions	3-9
signal.h – Signal Handling.....	3-9

sport.h – ADSP-218x Serial Ports	3-9
stdio.h – Standard Input/Output	3-9
sysreg.h.....	3-10
Library Structure	3-11
Documented Library Functions	3-13
C Run-Time Library Reference	3-17
abort	3-18
abs	3-19
acos	3-20
asin	3-21
atan	3-22
atan2	3-23
atexit	3-24
atof	3-25
atoi	3-26
atol	3-27
biquad	3-28
bsearch	3-31
calloc	3-33
ceil	3-34
clear_interrupt	3-35
copysign	3-37
cos	3-38
cosh	3-39

CONTENTS

demean_buffer	3-40
disable_interrupts	3-42
div	3-43
enable_interrupts	3-44
exit	3-45
exp	3-46
fabs	3-47
fftN	3-48
fir	3-51
floor	3-53
fmod	3-54
free	3-55
frexp	3-56
ifftN	3-57
iir	3-60
interrupt	3-64
io_space_read	3-67
io_space_write	3-68
isalnum	3-69
isalpha	3-70
isctrl	3-71
isdigit	3-72
isgraph	3-73
isinf	3-74

islower	3-76
isnan	3-77
isprint	3-79
ispunct	3-80
isspace	3-81
isupper	3-82
isxdigit	3-83
labs	3-84
ldexp	3-85
ldiv	3-86
log	3-87
log10	3-88
longjmp	3-89
malloc	3-91
memchr	3-92
memcmp	3-93
memcpy	3-94
memmove	3-95
memset	3-96
modf	3-97
perror	3-98
pow	3-99
printf	3-100
qsort	3-101

CONTENTS

raise	3-103
rand	3-106
realloc	3-107
setjmp	3-108
signal	3-109
sin	3-112
sinh	3-113
sqrt	3-114
srand	3-115
strcat	3-116
strchr	3-117
strcmp	3-118
strcoll	3-119
strcpy	3-120
strcspn	3-121
strerror	3-122
strlen	3-123
strncat	3-124
strncmp	3-125
strncpy	3-126
strpbrk	3-127
strrchr	3-128
strspn	3-129
strstr	3-130

strtod	3-131
strtodf	3-133
strtok	3-135
strtol	3-137
strtoul	3-139
strxfrm	3-141
sysreg_read	3-143
sysreg_write	3-145
tan	3-147
tanh	3-148
timer_off	3-149
timer_on	3-150
timer_set	3-151
tolower	3-153
toupper	3-154
va_arg	3-155
va_end	3-156
va_start	3-157

COMPILER LEGACY SUPPORT

Overview	A-1
Tools Differences	A-1
C Compiler and C Run-Time Library	A-3
Segment Placement Support Keyword Changed to Section ...	A-3
G21 Compatibility Call	A-3

CONTENTS

Support for G21-Based Options and Extensions	A-3
Indexed Initializers	A-4
Compiler Diagnostics	A-4
ANSI C Extensions.....	A-4
Compiler Switch Modifications.....	A-5
Warnings.....	A-8
Run-Time Model.....	A-9

INDEX