

W 2.0

C/C++ Compiler and Library Manual for TigerSHARC DSPs

Third Revision, July 2001

Part Number
82-001983-01

Analog Devices, Inc.
Digital Signal Processor Division
One Technology Way
Norwood, Mass. 02062-9106

a

Copyright Information

©1996–2001 Analog Devices, Inc., ALL RIGHTS RESERVED. This document may not be reproduced in any form without prior, express written consent from Analog Devices, Inc.

Printed in the USA.

Disclaimer

Analog Devices, Inc. reserves the right to change this product without prior notice. Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use; nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under the patent rights of Analog Devices, Inc.

Trademark and Service Mark Notice

The Analog Devices logo, VisualDSP, the VisualDSP logo, SHARC, and the SHARC logo are registered trademarks; VisualDSP++, the VisualDSP++ logo, CROSSCORE, the CROSSCORE logo, TigerSHARC, the TigerSHARC logo, Blackfin, the Blackfin logo, EZ-KIT Lite, Apex-ICE, Mountain-ICE, Summit-ICE, Trek-ICE, and The DSP Collaborative are trademarks of Analog Devices, Inc.

Microsoft and Windows are registered trademarks and Windows NT is a trademark of Microsoft Corporation.

Adobe and Acrobat are registered trademarks of Adobe Corporation.

Intel is registered trademark of Intel Corporation.

All other brand and product names are trademarks or service marks of their respective owners.

Revision 3.0

CONTENTS

INTRODUCTION

Supported Processors	1-2
For Additional Information about Analog Products	1-2
For Technical or Customer Support	1-2
Purpose of This Manual	1-3
Intended Audience	1-3
Manual Contents Description	1-4
What's New in This Manual	1-4
Related Documents	1-4
Conventions	1-6

COMPILER

Overview	2-1
Compiler Command-Line Reference	2-3
Running the Compiler	2-4
C/C++ Compiler Switches	2-9
C/C++ Compiler Switch Summaries	2-9
C/C++ Mode Selection Switch Descriptions.....	2-18

CONTENTS

C/C++ Compiler Common Switch Descriptions	2-19
C++ Compiler Switch Descriptions	2-40
Data Type Sizes	2-45
Integer	2-46
Floating Point.....	2-46
Data Type Alignment	2-47
Optimization Control	2-48
Inlining Control	2-50
Interprocedural Analysis	2-50
C/C++ Compiler Language Extensions	2-53
Inline Function Support Keyword (inline)	2-56
64-Bit Integer Support (long long)	2-57
Quad Word Support	2-57
Dual Memory Support Keywords (pm dm)	2-58
Memory Keywords and Assignments/Type Conversions	2-60
Memory Keywords and Function Declarations/Pointers	2-61
Memory Keywords and Function Arguments	2-62
Memory Keywords and Macros	2-63
__regclass Construct	2-63
Placement Support Keyword (section)	2-64
Boolean Type Support Keywords (bool, true, false)	2-65
Pointer Class Support Keyword (restrict)	2-65
Variable Length Array Support	2-66
Non-Constant Aggregate Initializer Support	2-68

Indexed Initializer Support	2-68
Built-In Functions	2-70
Data Types (16-Bit)	2-70
Data Types (32-Bit)	2-81
Math Intrinsics	2-82
Non-Standard Data Types	2-83
Preprocessor Generated Warnings	2-87
C++-Style Comments	2-87
C++ Fractional Type Support	2-88
Format of Fractional Literals	2-88
Conversions Involving Fractional Values	2-89
Fractional Arithmetic Operations	2-89
Mixed Mode Operations	2-90
Preprocessor Features	2-91
Predefined Macros	2-91
Header Files	2-94
Writing Macros	2-95
C/C++ Run-Time Model	2-97
Stack Frame	2-97
Parts of the Stack Frame	2-100
General System-wide Specifications	2-102
Argument Passage	2-103
Return Values	2-105
Procedure Call and Return	2-106

CONTENTS

Code Sequences	2-108
Miscellaneous Information	2-109
Register Classification	2-110
Callee Preserved Registers (“Preserved”)	2-110
Caller Save Registers (“Scratch”)	2-110
ADSP-TS001 and ADSP-TS101 Registers.....	2-111
C/C++ and Assembly Interface	2-116
Writing C/C++-Callable Assembly Subroutines	2-116
Calling C/C++ Routines from the Assembler	2-120
C/C++ Compiler Glossary	2-121

RUN-TIME LIBRARY

Overview	3-1
C and C++ Run-Time Libraries Guide	3-3
Calling Library Functions	3-3
Linking Library Functions	3-4
Working With Library Source Code	3-6
Working With Library Header Files	3-7
Standard C Library Header Files	3-8
Standard C Library Header File Descriptions.....	3-10
DSP Header Files	3-14
Abridged C++ Library Support	3-21
Embedded C++ Library Header Files.....	3-22
C++ Header Files for C Library Facilities.....	3-24
Embedded Standard Template Library Header Files	3-26

Run-time Library Reference	3-29
abs.....	3-30
acos	3-31
a_compress	3-32
addbitrev	3-33
a_expand	3-34
arg.....	3-35
asin.....	3-36
atan	3-37
atan2	3-38
atof.....	3-39
atoi.....	3-40
atol.....	3-41
atold.....	3-42
autocoh	3-43
autocorr.....	3-44
avg	3-45
bsearch	3-46
cabs	3-47
cadd	3-48
cdiv	3-49
ceil	3-50
cexp.....	3-51
cfft	3-52

CONTENTS

cfft2d	3-54
clip	3-56
cmatmadd	3-57
cmatmmlt	3-58
cmatmsub	3-59
cmatsadd	3-60
cmatsmlt	3-61
cmatssub	3-62
cmlt	3-63
conj.....	3-64
convolve.....	3-65
conv2d.....	3-66
copysign.....	3-67
cos	3-68
cosh	3-69
cot	3-70
count_ones.....	3-71
crosscoh	3-72
crosscorr.....	3-73
csub	3-74
cvecdot.....	3-75
cvecsadd	3-76
cvecsmult	3-77
cvecssub	3-78

cvecvadd	3-79
cvecvsub	3-80
cvecvmlt	3-81
div	3-82
exp	3-83
__emuclk.....	3-84
fir	3-85
fir_decima	3-87
fir_interp	3-88
floor	3-89
fmod	3-90
frexp.....	3-91
gen_bartlett	3-92
gen_blackman.....	3-94
gen_gaussian	3-95
gen_hamming	3-96
gen_hanning	3-97
gen_harris.....	3-98
gen_kaiser.....	3-99
gen_rectangular	3-100
gen_triangle.....	3-101
gen_vonhann	3-103
histogram	3-104
ifft	3-105

CONTENTS

ifft2d.....	3-107
iir.....	3-109
log	3-111
log10.....	3-112
matsadd	3-113
matmadd.....	3-114
matmmlt	3-115
matmsub	3-116
matsmlt.....	3-117
matssub.....	3-118
max.....	3-119
mean	3-120
min	3-121
modf	3-122
mu_compress	3-123
mu_expand	3-124
norm.....	3-125
polar	3-126
pow.....	3-127
qsort	3-128
rand	3-130
rfft	3-131
rfft2d	3-133
rms	3-135

rsqrt	3-136
sign	3-137
sin	3-138
sinh	3-139
sqrt.....	3-140
srand	3-141
strtod.....	3-142
strtof	3-143
strtoi	3-144
strtol.....	3-146
strtold.....	3-148
strtoul.....	3-149
tan.....	3-150
tanh.....	3-151
twidfft	3-152
var	3-154
vecdot.....	3-155
vecsadd	3-156
vecsmult	3-157
vecssub	3-158
vecvadd.....	3-159
vecvmlt.....	3-160
vecvsub	3-161
zero_cross	3-162

CONTENTS

INDEX