


NOTES:

1. POPULATE M1-M5 WITH RUBBER FEET. SEE SHEET 2 FOR LOCATION.
2. PLACE SERIAL NUMBER ON BOTTOM SIDE SEE SHEET 2 FOR LOCATION.
3. PLACE BOM REV ON BOTTOM SIDE SEE SHEET 2 FOR LOCATION.
4. U24 & U25 HAVE OPTIONAL MOUNTING FOR EITHER SMT OR THROUGH HOLE. USE PARTS SPECIFIED.
5. EITHER U24 OR Y2 WILL BE POPULATED. NEVER BOTH, USE PART SPECIFIED.
6. BEFORE WAVE SOLDERING MASK HOLES FOR P1,P3,P9,P10,P11,Y2 TP1-TP3.
7. BREAK OFF STRIP AT COMPLETION OF ASSEMBLY.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655
	APPROVALS	DATE	
MATERIAL	DRAWN	06/26/07	ASSEMBLY DRAWING TOP SIDE 21161N EZ-KIT LITE
FINISH	CHECKED		
DO NOT SCALE THIS DRAWING	ENGINEERING		SIZE B DWG. NO. ASSMAA0157-2000-REF
	QUALITY		
	MANUFACTURING		SCALE 1 : 1 SHEET 1 OF 2