

VISUALDSP++TM 2.0

User's Guide for ADSP-21xx DSPs

Third Revision, April 2001

Part Number
82-000349-01

Analog Devices, Inc.
Digital Signal Processor Division
One Technology Way
Norwood, Mass. 02062-9106

a

Copyright Information

©1996-2001 Analog Devices, Inc., ALL RIGHTS RESERVED. This document may not be reproduced in any form without prior, express written consent from Analog Devices, Inc.

Printed in the USA.

Disclaimer

Analog Devices, Inc. reserves the right to change this product without prior notice. Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use; nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under the patent rights of Analog Devices, Inc.

Trademark and Service Mark Notice

The Analog Devices logo, SHARC, the SHARC logo, TigerSHARC, the TigerSHARC logo, and EZ-LAB are registered trademarks; VisualDSP++, VDK, and the VisualDSP++ logo, Apex-ICE, Mountain-ICE, Summit-ICE, Trek-ICE, and The DSP Collaborative are trademarks of Analog Devices, Inc.

Microsoft and Windows are registered trademarks and Windows NT is a trademark of Microsoft Corporation.

Adobe and Acrobat are registered trademarks of Adobe Corporation.

All other brand and product names are trademarks or service marks of their respective owners.

Rev. 3.0

CONTENTS

INTRODUCTION

In This Chapter	1-1
About VisualDSP++	1-2
About This Manual	1-2
Purpose	1-2
Intended Audience	1-2
Contents Description	1-3
Conventions	1-4
How to Use VisualDSP++ Help	1-5
Related Documents	1-6
Information Services	1-7
For Product Information	1-7
For Technical or Customer Support	1-8

ABOUT VISUALDSP++

In This Chapter	2-1
What Is VisualDSP++?	2-2
VisualDSP++ Features	2-2
Integrated Development and Debugging Environment	2-2

CONTENTS

Code Development Tools	2-2
Source File Editing Features	2-3
Project Management Features	2-4
Debugging Features	2-5
VDK Features	2-6
Differences between Processor Families	2-8
New VisualDSP++ Features	2-9
Program Development	2-12
DSP Program Development	2-12
Simulation	2-12
Evaluation	2-12
Emulation	2-12
Simulation and Emulation	2-12
Targets	2-14
Simulation Targets	2-14
Emulation Targets	2-14
Platforms	2-15
Simulation	2-15
Emulation	2-15
Hardware Simulation	2-16
Debugging Overview	2-16
VisualDSP++ Kernel	2-17
Program Development Steps	2-18

Step 1: Create a Project	2-18
Step 2: Configure Project Options	2-19
Step 3: Add and Edit Project Source Files	2-19
Step 4: Define Project Build Options	2-20
Step 5: Build a Debug Version of the Project	2-21
Step 6: Create a Debug Session and Load the Executable	2-22
Step 7: Run and Debug the Program	2-22
Step 8: Build a Release Version of the Project	2-22
Code Development Tools	2-23
Compiler	2-24
Assembler	2-25
Linker	2-26
Splitter	2-27
Loader	2-28
File Associations	2-29
Linker Description Files	2-30
DSP Projects	2-31
What is a Project?	2-31
Flexibility	2-31
Project Options	2-32
Project Configurations	2-33
Customized Project Configurations	2-33
Project Build	2-34

CONTENTS

Build Options	2-35
Project Dependencies	2-36
Project Rules	2-37
Projects Built with VDK	2-38
Tcl Scripting	2-39
Analog Devices Tcl Commands	2-39
Tcl Output	2-39
Tcl Command Issuance	2-40
Extensive Scripting	2-40

ENVIRONMENT

In This Chapter	3-1
Parts of the User Interface	3-2
Title Bar	3-4
Additional Information in Title Bars	3-5
Title Bar Right-Click Menus	3-5
Control Menu	3-6
Program Icons	3-6
Editor Windows	3-7
Debugging Windows	3-7
Menu Bar	3-7
Command Information	3-8
Toolbars and User Tools	3-9
Built-In Toolbars	3-9

Toolbar Customization	3-10
Toolbars: Docked vs. Floating	3-11
Toolbar Button Appearance	3-12
Toolbar Shape	3-13
Toolbar Rules	3-14
User Tools	3-15
Status Bar	3-16
VisualDSP++ Windows	3-18
Project Window	3-18
Project Tab Page	3-19
Project Nodes	3-20
Project Tab Page Right-Click Menus	3-21
Project Folders	3-21
Project Files	3-22
Kernel Tab Page	3-23
Project Window Right-Click Menus	3-25
Automatic File Placement	3-29
Editor Windows	3-30
Output Window	3-32
Output Window Tabs	3-33
Output Window Customization	3-35
Log File	3-36
Right-Click Menu	3-37

CONTENTS

Environment Customization	3-38
User Preferences	3-38
Other Available Customizations	3-39
Work Environment Customization	3-40
Workspace Specification	3-41
Window Color Customization	3-41
Window Operations	3-45
Window Manipulation	3-45
Right-Click Menu Options	3-45
Scroll Bars and Resize Pull-Tab	3-46
Windows: Docked vs. Floating	3-46
Example of a Docked Window	3-47
Examples of Floating Windows	3-48
Window Position Rules	3-49
Standard Windows Buttons	3-50
Debugging Windows	3-51
Disassembly Windows	3-53
Other Disassembly Window Features	3-55
Right-Click Menu	3-55
Disassembly Window Symbols	3-56
Expressions Window	3-57
Trace Windows	3-58
Profile Windows	3-59

Profile Information	3-59
Right-Click Menu	3-60
Locals Window	3-61
Statistical/Linear Profiling Results Window	3-62
Left Pane	3-63
Right Pane	3-64
Right-Click Menu	3-64
Call Stack Window	3-66
Memory Windows	3-67
Right-Click Menu	3-69
Memory Window Display Customization	3-69
Memory Map Windows	3-70
Register Windows	3-71
Register Windows and Stack Windows	3-72
Stack Windows	3-72
Custom Register Windows	3-72
Multiprocessor Window	3-73
Multiprocessor Groups	3-73
Focus	3-74
Right-Click Menu	3-74
Multiprocessor Window Tabs	3-75
Pipeline Window	3-76
VDK Status Window	3-77

CONTENTS

State History Window	3-79
Thread Status and Event Colors	3-80
Window Operations	3-80
Actions You can Perform from the Plot	3-81
Target Load Window	3-82
About Debugging Windows	3-83
Editor Window Features	3-83
Editor Window Symbols	3-85
Bookmarks	3-85
Context-Sensitive Expression Evaluation	3-86
Source Mode vs. Mixed Mode	3-87
Expressions in an Expressions Window	3-89
About Expressions	3-90
Number Formats	3-91
Plot Windows	3-93
Plot Window Features	3-94
Plot Configuration	3-97
Plot Window Presentation	3-98
Plot Presentation Options	3-100

DEBUGGING

In This Chapter	4-1
Debug Sessions	4-2
Debug Session Management	4-3

Simulation vs. Emulation	4-3
MP Debug Sessions vs. Single-Processor Debug Sessions	4-4
Breakpoints	4-4
Watchpoints	4-4
Multiprocessor (MP) Debugging Session	4-5
Multiprocessor Debugging	4-6
Focus and Pinning	4-7
Window Title Bar Information	4-8
Additional Focus Indication	4-8
Code Behavior Analysis	4-9
Code Analysis Tools	4-9
Traces	4-9
Profiles	4-9
Statistical Profiles and Linear Profiles	4-9
Traces	4-10
Profiling Code	4-10
Statistical Profiling vs. Linear Profiling	4-11
Simulation	4-11
Emulation	4-12
DSP Memory Plots	4-13
Program Execution Operations	4-14
Program Loading	4-14
Program Execution Operations	4-14

CONTENTS

Commands for Multiprocessor Debug Sessions	4-15
Commands	4-15
Program Restart	4-16
Performing a Restart during Simulation	4-16
Performing a Restart during Emulation	4-16
Breakpoints	4-17
Unconditional vs. Conditional Breakpoints	4-18
Watchpoints	4-18
Simulation Tools	4-19
Interrupts	4-19
Processor Boot Simulation	4-19
Data Input/Output Simulation (Streams)	4-19
Plots	4-20
Plot Types	4-20
Line Plots	4-21
X-Y Plots	4-22
Constellation Plots	4-23
Eye Diagrams	4-24
Waterfall Plots	4-26
Spectrogram Plots	4-28

REFERENCE INFORMATION

In This Appendix	A-1
Glossary	A-2
C++ Run-Time Libraries	A-13
File Types	A-14
Keyboard Shortcuts	A-16
Working with Files	A-16
Moving within a File	A-17
Cutting, Copying, Pasting, Moving Text	A-18
Selecting Text within a File	A-19
Working with Bookmarks in an Editor Window	A-20
Building Projects	A-20
Program Execution	A-21
Working with Breakpoints	A-22
Working with Multiprocessor Systems	A-22
Obtaining Online Help	A-23
Miscellaneous	A-23
Keyboard Shortcuts for Changing Focus	A-24
IDDE Command-Line Parameters	A-25
Toolbar Buttons	A-26
Text Operations	A-32
Regular Expressions in Find/Replace Operations	A-32
Regular Expressions vs. Normal Searches	A-32

CONTENTS

Specific Special Characters	A-33
Special Rules for Sequences	A-34
Repetition and Combination Characters	A-35
Match Rules	A-36
Tagged Expressions in Replace Operations	A-36
Comment Start and Stop Strings	A-38

ADSP-2191 PERIPHERALS USED WITH THE SIMULATOR

In This Appendix	B-1
General-Purpose IO (GPIO) or Flag IO (FIO) Peripheral	B-2
Overview of GPIO in the Simulator	B-2
Input and Output Handling	B-4
GPIO Window in VisualDSP++	B-4
Example – GPIO Test	B-5
Host Port Interface (HPI) Peripheral	B-8
Overview of HPI in the Simulator	B-8
Input and Output	B-9
Commands for the External Initiated Control File	B-10
Command Bit Definitions	B-11
External Initiated Direct Operation Bit Definitions	B-12
Host Port Window in VisualDSP++	B-13
Unsupported Features	B-14
Example – DMA Transfer to the Host Port	B-14

Serial Peripheral Interface (SPI)	B-17
Overview of SPI in the Simulator	B-17
Global Status and Control	B-18
SPI Signal Usage	B-19
Modes of Operation	B-20
Master Mode Operation (no DMA)	B-20
Slave Mode Operation (no DMA)	B-20
Master Mode DMA Operation	B-21
Slave Mode DMA Operation	B-22
SPI with Streams	B-23
Master Mode Example (No DMA)	B-24
Slave DMA Mode Example	B-26
Serial Port (SPT) Peripheral	B-33
Overview of SPT in the Simulator	B-33
Input and Output	B-35
Serial Port Windows in VisualDSP++	B-36
Unsupported Features	B-36
Example	B-37
Serial Port (UART) Peripheral	B-43
Overview of UART in the Simulator	B-43
Input and Output	B-45
UART Window in VisualDSP++	B-45
Unsupported Features	B-45

CONTENTS

Example	B-46
Timer (TMR) Peripheral	B-53
Overview of TMR in the Simulator	B-53
Global Status and Control	B-54
Timer Signal Usage	B-56
Modes of Operation	B-56
Timer with Streams Usage	B-57
WIDTH_CAP Mode	B-57
Example – WIDTH_CAP Mode with Streams	B-58
External Clock Mode	B-60
Memory DMA (MEMDMA) Peripheral	B-61
Overview of MEMDMA in the Simulator	B-61
Modes	B-61
Registers	B-62
Example – MEMDMA Transfer	B-64
 TCL SCRIPTING	
In This Appendix	C-1
Overview	C-1
Tcl Output and Command Issuance	C-2
Command-Line Issuance	C-2
Output Window Issuance	C-2
Menu Issuance	C-3
Editor Window Issuance	C-3

User Tool Issuance	C-3
Tcl Command Listings and Examples	C-4
Target Query and Manipulation Commands	C-4
GUI Manipulation Commands	C-7
Project Build and Maintenance Commands	C-8
Tcl Script Example	C-9
Example Regression Test	C-10
Tcl Command Reference	C-16
dspaddmenuitem	C-16
dspcancelbreak	C-18
dspcheckmenuitem	C-19
dspclickmenuitem	C-20
dspdeletemenuitem	C-21
dspenablemenuitem	C-22
dspeval	C-23
dspgetbreak	C-25
dspgetmemblock	C-27
dspgetmeminfo	C-29
dspgetprocessors	C-30
dspgetstate	C-30
dspgetswstack	C-31
dsphalt	C-32
dspload	C-33

CONTENTS

dsplookupline	C-34
dsplookupsymbol	C-35
dspmemorywin	C-36
dspplotrotate	C-37
dspplotwin	C-38
dspprojectaddfile	C-41
dspprojectaddfolder	C-42
dspprojectbuild	C-43
dspprojectclose	C-44
dspprojectinfo	C-45
dspprojectload	C-46
dspprojectremovefile	C-46
dspprojectremovefolder	C-47
dspregisterwin	C-48
dspreset	C-49
dsprestart	C-50
dsprun	C-51
dspset	C-52
dspsetbreak	C-53
dspsetmemblock	C-55
dspsetswstack	C-57
dspstepasm	C-58
dspstepin	C-59

dspstepout	C-60
dspstepover	C-61
dspwaitforhalt	C-62
Additional Tcl Resources	C-62

INDEX

CONTENTS