





- NOTES:
1. POPULATE M1-M5 WITH RUBBER FEET. SEE SHEET 2 FOR LOCATION.
  2. PLACE SERIAL NUMBER ON BOTTOM SIDE SEE SHEET 2 FOR LOCATION.
  3. PLACE BOM REV ON BOTTOM SIDE SEE SHEET 2 FOR LOCATION.
  4. BEFORE WAVE SOLDERING MASK HOLES FOR TP1-TP8.
  5. BREAK OFF STRIPS AT COMPLETION OF ASSEMBLY.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655
	APPROVALS	DATE	
MATERIAL	DRAWN	06/25/07	ASSEMBLY DRAWING TOP SIDE ADSP-21262 EZ-KIT LITE
FINISH	ENGINEERING		
DO NOT SCALE THIS DRAWING	MANUFACTURING		SIZE B DWG. NO. ASSMAA0174-2002-REF REV. 2.0
SCALE 1:1		SHEET 1 OF 2	




UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655	
	APPROVALS	DATE		
MATERIAL	DRAWN	06/25/07	ASSEMBLY DRAWING BOTTOM SIDE ADSP-21262 EZ-KIT LITE	
FINISH	ENGINEERING			
DO NOT SCALE THIS DRAWING	MANUFACTURING		SIZE B	REV. 2.0
		SCALE 1 : 1	DWG. NO. ASSMAA0174-2002-REF	SHEET 2 OF 2





UNLESS OTHERWISE SPECIFIED

- BOARD TO BE FABRICATED PER IPC-6012A, CLASS 2.
- MATERIAL: POLYCLAD FR-370HR OR EQUIVALENT. OUTER LAYERS 1/2 OZ/SQFT CU  
INNER LAYERS 1/2 OZ/SQFT CU FINISHED .062 (.055 MIN .070 MAX SEE DETAIL).  
VENDOR MAY ADJUST THICKNESS TO FULFILL NOTE 9.
- PLATING: ADDITIONAL CU PLATING 1 OZ/SQFT  
ALL HOLES PLATED THROUGH, EXCEPT AS NOTED IN HOLE LEGEND.  
MINIMUM PTH BARREL THICKNESS = 0.0008" MINIMUM AVERAGE  
PER IPC-6012A WITH AMENDMENT 1, CLASS 2 REQUIREMENTS.  
WITH NO SINGLE MEASUREMENT LESS THAN 0.00071 IN THE PLATED HOLES.
- FINISH: SURFACES TO BE COATED BY ENIG OF 2 TO 10 MICROINCHES OVER  
A MINIMUM OF 60-200 MICROINCHES OF LOW STRESS NICKEL.  
NO ADDITIONAL ELECTROLYTIC HARD GOLD IS REQUIRED FOR CONTACTS.
- SOLDERMASK: SOLDER MASK TO BE TRANSPARENT GREEN LPI BOTH SIDES PER GERBER FILES.
- SILKSCREEN: WHITE EPOXY INK, APPLY TO BOTH SIDES PER GERBER FILES.
- ARTWORK: MINIMUM FEATURE SIZE = 0.00492  
MINIMUM AIR GAP = 0.00475
- ALL DIMENSIONS ARE IN INCHES.
- CONTROLLED IMPEDANCE: BOARD TO BE BUILT TO YIELD CONTROLLED IMPEDANCE  
OF 60 OHMS +/- 10% ON ALL .00492" LINE WIDTHS
- DO NOT ADD NON-FUNCTIONAL COPPER THIEVING ON OPEN AREAS OF OUTER LAYERS.  
THIEVING IS ALLOWED ON INNER LAYERS, UNLESS OTHERWISE SPECIFIED.
- VIAS SHOULD BE COVERED ACCORDING TO ONE OF THE FOLLOWING METHODS.  
METHOD 1 IS PREFERRED.  
METHOD 1: VIAS MUST BE FILLED WITH SOLDERMASK MATERIAL AFTER  
ELECTROLESS NICKEL/IMMERSION GOLD AND BEFORE PRIMARY LPI MASK. AFTER THE  
FILL IS CURED, THE PRIMARY MASK IS THEN APPLIED WITH NO VIA APERTURES  
BOTH SIDES.  
METHOD 2: AFTER APPLICATION OF FULL BODY ELECTROLESS NICKEL/IMMERSION  
GOLD, APPLY PRIMARY MASK WITH REDUCED VIA APERTURES THAT ARE 6 MILS  
LARGER THAN DRILLED HOLE DIAMETER BOTH SIDES. THEN APPLY SOLDER MASK  
PLUG ON COMPONENT SIDE.
- VIA HOLES (.006, .010, .014) REQUIRE TANGENCY ONLY, INSTEAD OF ANNULAR RING.
- TEARDROP PADS ARE ACCEPTABLE WHERE NEEDED.
- BUILD AS 1-UP PCB.
- USE IPC-D-356A NETLIST AS SUPPLIED FOR CHECKING.
- V SCORE 2 LINES ON BOTH SIDES OF THE BOARD. SEE DETAIL.


SIZE	QTY	SYM	PLATED	TOL
6	113	+	YES	+0.003-0.006
10	21	X	YES	+0.003-0.010
14	809	□	YES	+0.003-0.014
37	58	◇	YES	+/-0.003
41	20	⊠	YES	+/-0.003
51	10	⊠	YES	+/-0.003
59	5	+ <sup>A</sup>	YES	+/-0.003
70	5	+ <sup>B</sup>	YES	+/-0.003
85	3	+ <sup>C</sup>	YES	+0.003-0.000
125	11	+ <sup>D</sup>	YES	+/-0.005
53	6	+ <sup>E</sup>	NO	+0.003-0.000
67	3	+ <sup>F</sup>	NO	+/-0.003
140	4	+ <sup>G</sup>	NO	+/-0.005
187	1	+ <sup>H</sup>	NO	+/-0.005
125	3	+ <sup>J</sup>	NO	+/-0.003





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655	
	APPROVALS	DATE		
MATERIAL SEE NOTES	DRAWN	06/25/07	FABRICATION DRAWING ADSP-21262 EZ-KIT LITE	
	CHECKED			
FINISH SEE NOTES	ENGINEERING		SIZE B	REV. 2.0
	QUALITY			
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1	SHEET 1 OF 1










UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b> 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655			
	APPROVALS	DATE				
	MATERIAL	DRAWN	06/25/07	LAYER 1 TOP SIDE ADSP-21262 EZ-KIT LITE		
		CHECKED				
FINISH	ENGINEERING		SIZE B	DWG. NO. A0174-2002-REF	REV. 2.	
	QUALITY					
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 1 OF 14	





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b>		20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655		
	APPROVALS	DATE					
	MATERIAL	DRAWN	06/25/07	LAYER 2 GROUND PLANE ADSP-21262 EZ-KIT LITE			
		CHECKED					
FINISH	ENGINEERING		SIZE B	DWG. NO. A0174-2002-REF	REV. 2.0		
	QUALITY						
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 2 OF 14		





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655		
	APPROVALS	DATE			
	MATERIAL	DRAWN	06/25/07	LAYER 3 INTERNAL SIGNAL ADSP-21262 EZ-KIT LITE	
		CHECKED			
FINISH	ENGINEERING		SIZE B	DWG. NO. A0174-2002-REF	REV. 2.0
	QUALITY				
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 3 OF 14








UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655	
	APPROVALS	DATE		
MATERIAL	DRAWN	06/25/07	LAYER 4 3V PLANE ADSP-21262 EZ-KIT LITE	
	CHECKED			
FINISH	ENGINEERING		SIZE B	DWG. NO. A0174-2002-REF
	QUALITY			
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1	SHEET 4 OF 14
			REV. 2.0	





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655		
	APPROVALS	DATE			
	MATERIAL	DRAWN	06/25/07	LAYER 5 5V PLANE ADSP-21262 EZ-KIT LITE	
		CHECKED			
FINISH	ENGINEERING		SIZE	DWG. NO.	REV.
	QUALITY		B		
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1	SHEET 5 OF 14	
			A0174-2002-REF		2.0





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b>		20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655	
	APPROVALS	DATE				
MATERIAL	DRAWN	06/25/07	LAYER 6 INTERNAL SIGNAL ADSP-21262 EZ-KIT LITE			
	CHECKED					
FINISH	ENGINEERING		SIZE B	DWG. NO.	A0174-2002-REF	REV. 2.0
	QUALITY					
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 6 OF 14	





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b>		20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655		
	APPROVALS	DATE					
	MATERIAL	DRAWN	06/25/07	LAYER 7 GROUND PLANE ADSP-21262 EZ-KIT LITE			
		CHECKED					
FINISH	ENGINEERING		SIZE B	DWG. NO.	REV. 2.		
	QUALITY						
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 7 OF 14		
			A0174-2002-REF				





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b>		20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655		
	APPROVALS	DATE					
	MATERIAL	DRAWN	06/25/07	LAYER 8 BOTTOM SIDE ADSP-21262 EZ-KIT LITE			
		CHECKED					
FINISH	ENGINEERING		SIZE B	DWG. NO. A0174-2002-REF	REV. 2.0		
	QUALITY						
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 8 OF 14		




UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b> 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655			
	APPROVALS	DATE				
	MATERIAL	DRAWN	06/25/07	SOLDER MASK TOP SIDE ADSP-21262 EZ-KIT LITE		
		CHECKED				
FINISH	ENGINEERING		SIZE B	DWG. NO. A0174-2002-REF	REV. 2.	
	QUALITY					
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 9 OF 14	





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b> 20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655			
	APPROVALS	DATE				
	MATERIAL	DRAWN	06/25/07	SOLDER MASK BOTTOM SIDE ADSP-21262 EZ-KIT LITE		
		CHECKED				
FINISH	ENGINEERING		SIZE B	DWG. NO.	A0174-2002-REF	REV. 2.0
	QUALITY					
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 10 OF 14	



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b>		20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655	
	APPROVALS	DATE				
	MATERIAL	DRAWN	06/25/07	SOLDER PASTE TOP SIDE ADSP-21262 EZ-KIT LITE		
		CHECKED				
FINISH	ENGINEERING		SIZE B	DWG. NO.	A0174-2002-REF	REV. 2.
	QUALITY					
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1		SHEET 13 OF 14	





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE : .XX +/- .010 .XXX +/- .005	CONTRACT NO.		 <b>ANALOG DEVICES</b>		20 Cotton Road Nashua, New Hampshire 03063 (603) 883-2430 FAX (603) 882-2655		
	APPROVALS	DATE					
	MATERIAL	DRAWN	06/25/07	SOLDER PASTE BOTTOM SIDE ADSP-21262 EZ-KIT LITE			
		CHECKED					
FINISH	ENGINEERING		SIZE B	DWG. NO.	REV.		
	QUALITY						
DO NOT SCALE THIS DRAWING	MANUFACTURING		SCALE 1 : 1	SHEET 14 OF 14			
			A0174-2002-REF				
			2.0				